



## Professionally approved products.

Datasheet

# 10m Long 138 bar Copper Tubing, -50 → +200°C

RS Stock number 0846519



### Features

Standard Duty, Annealed Copper Tube

Annealed, standard duty copper tube

Use with Enots compression fittings

Operating Temperature Range -50 → +200 °C

CW024A grade

Warning: The 3/16 in. copper tube, should not be used as brake pipe copper tube which has a different internal diameter