



9	Washer	Brass	Nickel Ptd.	1
8	Screw Nut	Brass	Nickel Ptd.	1
7	Housing	PA66		1
6	Insulator	Bakelite Paper Sheet		2
5	Pin	Copper	Nickel Ptd.	1
4	Bushing	Brass	Nickel Ptd.	1
3	Pin Terminal	Brass	Silver Ptd.	1
2	Break Terminal	Brass	Silver Ptd.	1
1	Sleeve Spring	PBS	Silver Ptd.	1
No.	Description	Material	Treat	Q'ty

specification
contact resistance :
30mΩ MAX (initial)
insulation resistance :
MIN 100 MEGΩ @500V DC
voltage withstand :
500V AC R.M.S. for 1 minute
life time :
5,000 cycles min.

品名: ITEM :	2.5X5.5 DC SOCKET PANEL MOUNT		一般公差	SHEET:	單位: unit:	mm	日期: date:	'07/01/23	繪圖: drwn by:	DanielShyr
料號: PART NO.	487842	圖號: DRW NO.	.X +/-0.25 .XX +/-0.10	1 1	比例: scale:	2 : 1	版本: version:	V. 1.0	核准: aprld by:	SkyShyr