

DATA SHEET: T5 EM BATTEN SERIES



230V T5 Emergency Batten



RS Stock No.:	851-3015	851-3012	851-3024	851-3030	851-3034	851-3040
Description:	IP20 T5 Batten EM Series					
Finishes:	White					
Weight (kg):	2.225	2.5	2.5	2.65	2.8	2.8
Wattage (W):	28	35	49	2 x 28	2 x 35	2 x 49
Total circuit Power (W):	31	38	44	62	75	106
Overall length (mm):	1175 (l)	1475 (l)	1475 (l)	1475 (l)	1475 (l)	1475 (l)
Input voltage:	230V 50Hz					
Lamp Type:	T5					
Construction:	Pressed Steel with Polycarbonate end caps					
Control gear:	High Frequency soft start ballast					
Class:	Class I					
IP rating:	IP20					
Warranty:	1 Year					
Photometric data:	No					
Dimmable:	No					
Instruction sheet:	Yes					
Origin of Manufacture:	China					
Quality assurance system:	ISO 9001					
Declaration of Conformity (held on file):	Yes					
Manufactured & accordance with:	EN60598					

