

Datasheet

RS Pro Eyebolt M10

RS Stock No: **673-692**



Product Details

RS Pro eyebolt with M10 thread size, is suitable for use in a wide range of lifting applications. This eyebolt is proof tested and supplied completely with test certificate. It is a high quality metric eyebolt with collar to BS4278. This eyebolt made of carbon steel, has a diameter of 15 mm.

Features and Benefits

- M10 thread size
- 15 mm thread length
- Made of carbon steel
- 0.25t working load limit



Specifications:

Diameter	15 mm
Material	Carbon Steel
Thread Length	18 mm
Thread Size	M10
Working Load Limit	0.25 t
Collar Diameter	22 mm
Collar Thickness	7 mm
Eye Outside Diameter	33 mm
Overall Height	54 mm
Standards Met	BS 4278:1984