

Low Profile Foot Switch



Degree of protection	IP20
Materials of Construction	Cast Aluminium cover & base.
Colour	Black
Cable Connection	Provided with a reversible strain relief clamp that accommodates a wide variety of cable sizes.
Contact Action	Momentary SPDT
Electrical Rating	20A 125-250V a.c., 0.75kW 125-250V a.c.
Features & Benefits	Low profile reduces operator fatigue. Nonskid base pads.
Weight	0.5kg
Size	(See below)

