

# Moulded Momentary Foot Switch



|                                  |  |
|----------------------------------|--|
| <b>Degree of protection</b>      | IP20   |
| <b>Materials of Construction</b> | Corrosion proof reinforced polymeric.  |
| <b>Colour</b>                    | Dark Grey.   |
| <b>Cable Connection</b>          | Adjustable strain relief clamp accommodates a wide range of cable sizes.                     |
| <b>Contact Action</b>            | DPDT Momentary.  |
| <b>Electrical Rating</b>         | 15A 125-250V a.c, 0.375kW 125-250V a.c.  |
| <b>Features &amp; Benefits</b>   | Flame retardant.<br>Raised ribs on operating cover ensures good grip.<br>Non-skid base pads. |
| <b>Weight</b>                    | 0.1kg  |
| <b>Size</b>                      | (See below)  |

