



ENGLISH

Datasheet

Stock No: 809-346

RS Pro S2107, Electronic Lighting Starter, 16 → 75 W, 240 V ac



Product Details

Fluorescent Lamp Starters

Two styles available, electronic and glow

Glow type incorporates a RF suppressor

Electronic type has built in failed lamp shut down safety circuit

Flicker free electronic start

All starters rated at 230Vac except series type which are rated at 110Vac

Note

Series type are rated at 110Vac and should only be used in 230Vac circuits when two lamps are series connected



ENGLISH

Specifications:

Type	Electronic
Wattage	16 → 75 W
Voltage Rating	240 V ac
Number of Lamps	1
Failed Lamp Shutdown Time	5s
Length	35 mm
Diameter	21.5mm