



ENGLISH

Datasheet

Stock No: 809-352

RS Pro S2108, Electronic Lighting Starter, 18 → 20 W, 110 V ac



Product Details

Fluorescent Lamp Starters

- Two styles available, electronic and glow
- Glow type incorporates a RF suppressor
- Electronic type has built in failed lamp shut down safety circuit
- Flicker free electronic start
- All starters rated at 230Vac except series type which are rated at 110Vac

Note:

Series type are rated at 110Vac and should only be used in 230Vac circuits when two lamps are series connected



ENGLISH

Specifications:

Type	Electronic
Wattage	18 → 20 W
Voltage Rating	110 V ac
Number of Lamps	2
Failed Lamp Shutdown Time	5s
Length	35 mm
Diameter	21.5mm