



ENGLISH

Datasheet

Stock No: 419-738

RS Pro Black SPST Rocker Switch



Product Details

RS Rocker Switches

SPST rocker switches, available in black, red spot or red illuminated versions

Panel cut out 27.8 x 13.8mm

Fitted with 6.35mm blade style terminals

Snap-in mounting, easy to install into panels with 0.75mm to 3mm thickness

Nylon Housing to UL 94V-2 with silver plated brass terminals

Illuminated versions available with 100-125Vac or 220-250Vac neons

For Illuminated Paddle Style rocker switches see stock no. 419-845

Approvals

CSA (File no. LR45128), VDE (File no. 11037-4401), UL, ENEC, CQC

27.2 to 29.4mm Height Panel Cut Out



ENGLISH

Specifications:

Contact Configuration	SPST
Switch Operation	On-Off
Panel Cut Out Width	28mm
Panel Cut Out Height	13.8mm
Contact Current Rating	16 A@ 125 V ac
Actuator Colour	Black
Mounting Type	Panel
Terminal Type	Quick Connect
Panel Cut Out Size	13.8 x 28mm
Case Material	Nylon
Contact Resistance	50mΩ