

ENGLISH

Datasheet

RS Pro 3168 Piece Stainless Steel Screw/Bolt Kit, M2, M2.5, M3, M4, M5, M6

RS Stock No: 281-984



Product Details

RS Pro screw/bolt kit contains 3168-pieces of M2, M2.5, M3, M4, M5 and M6 threaded screws. The screw/bolt with pozidriv drive, is made of A2 grade 18/8 stainless steel.

Features and Benefits

- Flat, pan head
- Machine screw
- Sold as pack of 3168




ENGLISH

Specifications:

Drive Type	Pozidriv
Finish	Plain
Head Shape	Flat, Pan
Material	Stainless Steel
Number of Pieces	3168
Screw/Bolt Length Longest	25 mm
Screw/Bolt Length Shortest	6 mm
Screw/Bolt Type	Machine Screw
Screw/Bolts Lengths	6 to 25 mm
Stainless Steel Type	304, A2
Thread Size	M2, M2.5, M3, M4, M5, M6
Specification	DIN 965, DIN 7985, DIN 934, DIN 125A, DIN 125B



281-984



- (GB) Machine Screw Kit ISO Metric (Pozidriv) Stainless Steel
- D ISO metrisches Maschinenschrauben-Sortiment (Pozidriv) Rostfreier Stahl
- F Kit de vis au pas metrique a empreinte cruciforme en acier inoxydable A2
- Corredo di vita a macchina metriche ISO (pozidriv) in acciaio inossidabile
- Juego de tornillos para metales, ISO, de rosca métrica (pozidriv), acero inoxidable

