


ENGLISH

Datasheet SPDT Slide Switch

RS Stock number 734-7334



SPECIFICATIONS

MECHANICAL LIFE: 30,000 make-and-break cycles. CONTACT RESISTANCE: 10m Ω max. Initial @ 2-4VDC 100mA for both silver and gold plated contacts. INSULATION RESISTANCE: 1,000M Ω min. DIELETRIC STRENGTH: 1,000 V RMS@sea level. OPERATING TEMPERATURE: -30° C to 85° C. MATERIALS CASE: Dlally phthalate (DAP) (UL94v-0). ACTUATOR: Nylon,black std. HOUSING: Stainless Steel. CONTACT:Silver or gold plated. TERMINAL SEAL: Epoxy. RoHS: 2002/95/EC RATING R : 0.4 Volt-Amps(VA) max. @20V max.(AC or DC)


- Q : 2Amps @250VAC
- 5Amps @120 VAC or 28 VDC


RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.




ENGLISH

Dimensions – inch mm







P.C. MOUNTING .185 4.70 4.70 0.073 Ø1.85

Model No.	POS.1	POS.2	POS.3
	÷.	, fin	H
5MS3	ON	OFF	ON
Term. Comm.	2-1	OPEN	2-3
SCHEMATIC	2 Comm. 3		2 Comm. 3

SWITCH FUNCTION

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.