

## Key features

- For hard and chemically aggressive waters
- Incoloy 825 sheathed elements 2 1/4 BSP threaded brass heads
- Control thermostat in Incoloy 825 pocket
- Corrosion resistant polypropylene terminal enclosure which can be angularly rotated to any position



## Product variations

Name	Code	Description
RY936	60390312	
RY1236	60391314	
RY1224	60391313	
RY927	60391311	
RY914	60391310	
RY724	60391309	
RY630	60391307	
RY616	60391306	
RY416	60391305	
RY411	60391304	
RY330	60391303	
RY311	60391302	
RY211	60391301	

**21/4" BSP complete with Thermostat & Incoloy 825 Elements** \*Not recommended for aggressive water

Catalogue No.	Short Code	Loading kW	Phases	Immersed Length	Thermostat
60-391301	RY211	2	1 only	1 1	Yes
60-391032	RY311	3	1 or 3	1 1	Yes
60-391303	RY330	-	1 or 3	3 0	Yes
60-391304	RY411	4	1 or 3	1 1	Yes
60-391305	RY416	-	1 or 3	1 6	Yes
60-391306	RY616	6	1 or 3	1 6	Yes
60-391307	RY630	-	1 or 3	3 0	Yes

**21/4" BSP complete with Thermostat & Incoloy 825 Elements** \*Not recommended for aggressive water

Catalogue No.	Short Code	Loading kW	Phases	Immersed Length	Thermostat
60-391309	RY724	7.5	1 or 3	2 4	Yes
60-391310	RY914*	9	1 or 3	1 4	Yes
60-391311	RY927	-	1 or 3	2 7	Yes
60-390312	RY936	-	1 or 3	3 6	Yes
60-391313	RY1224	1 2	1 or 3	2 4	Yes
60-391314	RY1236	-	1 or 3	3 6	Yes