



ENGLISH

Datasheet

Stock No: 379-722

RS Pro Trace Heating Tape Constant Wattage



Product Details

Silicone Insulated Heating Tape

Parallel circuit, constant 10W output per metre heating tapes terminated in 1.3m of 2-core mains cable.

Features and Benefits

- May be looped around an enclosure, avoids localised hot spots
- Operating temperature range -70 to +200°C
- Supply voltage 240Vac

Constant Wattage Fixed Circuit Heating Cable



ENGLISH

Specifications:

Cable Type	Constant Wattage, Parallel Circuit
Voltage Rating	240 V
Minimum Operating Temperature	-70°C
Maximum Operating Temperature	+200°C
Operating Temperature Range	-70 → +200 °C
Length	3m
Sheath Material	Silicone Rubber