



Datasheet

Stock No: 208-6040

ENGLISH

# RS Pro PUR Tyred Wheel, 350kg



## Product Details:

### Polyurethane Tyre, Heavy Duty Cast Iron Wheel, PCB Series

- Cast polyurethane tyre, hardness Shore A95
- Cast iron hub
- Temperature range -30°C to +80°C

### Industrial - Polyurethane Tyre

Polyurethanes have very high load capacity, abrasion and tear resistance, soft ride and chemical resistance. Temperature range: -30 to +90°C.

## Specifications:

Load Capacity:	350kg
Tyre Type:	Solid
Tyre Material:	PUR
Hub Material:	Cast Iron
Features:	Abrasion Resistant, Corrosion Resistant
Hub Bearing Type:	Double Ball Race
Wheel Diameter:	100mm
Wheel Width:	40mm
Bore Diameter:	125mm
Bore Length:	47mm