

Surge Strips with USB Charging



- 6 AC outlets 120V / 15A
- 2 USB ports 5V / 2.1A
- 900 joule surge protection
- EMI/RFI noise protection
- Circuit breaker switch
- 6 ft. power cord
- Response time of <1ns
- Indoor use
- ETL approved
- Lifetime Warranty



Fig. 1



Fig. 2

**LIFETIME
WARRANTY**



Item#	Figure	Color	AC Outlets	USB Ports	Cord Length	Outlet Position	Lit Power Switch	EMI/RFI	Surge Protected
EPD-1926B	FIG. 1	BLACK	6	2	6 FT.	90 DEGREE	YES	YES	YES
EPD-1926W	FIG. 2	WHITE	6	2	6 FT.	90 DEGREE	YES	YES	YES

Specifications

Item#	Wire AWG	AC Power	USB Charge Volts/Amps	Surge Protected	Joule Ratings	Clamping Voltage	Max Spike Current
EPD-1926B	SJT 14AWG/3C	15A/125V/60HZ/1875W	5V / 2.1A MAX	YES	900	500V	45,000A
EPD-1926W	SJT 14AWG/3C	15A/125V/60HZ/1875W	5V / 2.1A MAX	YES	900	500V	45,000A