



[Home](#) | [Sign In](#) | [Contact Us](#)

SEARCH

Go



Combo D (Connectors)



PART NUMBER: DDM24W7SA197

Where Sold	Americas, Europe
Product Group	D-Subminiature
Product Sub-Family	D-Sub Combo
Component Type	Connector
Application Type	Commercial
Cable or PC Board	Cable
Gender	Receptacle
Number of Signal Pins	17
Number of Size 8 contacts	7
Straight or Right Angle	Straight
Contact Plating	Gold over Nickel
Shell Plating	Tin
Hardware	3,05 (.120) Through Holes
Contact Termination	Solder Cup
Shell Size	DD
Temperature Rating	-55°C to +125°C
Current Capacity	7.5 A
Contact Resistance	8 milli ohms max.
Dielectric Withstanding Voltage	1250 V AC at Sea Level
Reference Industry Specifications	Mil-PRF-24308
Insulator Material	Black Polyester UL 94V-0
Contact Material	Copper Alloy
Shell Material	Steel
Other Information	See Size 8 Contacts for Coax, High Power, and High Voltage Contacts

 Sales

 Ask a

 Prod

 Stock

 Dime
Draw

 PRI

[Home](#) | [About ITT](#) | [Products](#) | [Design Center](#) | [Literature](#) | [News & Events](#) | [Search Tools](#) | [G Support](#)

© ITT Corporation. All rights reserved. [Legal Disclaimer](#) | [Privacy Policy](#) | [General Terms](#) | [Channel Partners Sign-In](#)