



[Home](#) | [Sign In](#) | [Contact Us](#)

SEARCH

Go



Combo D (Connectors)



PART NUMBER: DCMM8W8P

Where Sold	Europe, Americas, Asia Pacific
Product Group	D-Subminiature
Product Sub-Family	D-Sub Combo
Component Type	Connector
Application Type	Military/High Reliability
Cable or PC Board	Cable
Gender	Plug
Number of Signal Pins	0
Number of Size 8 contacts	8
Straight or Right Angle	Straight
Contact Plating	50 micro inches Gold over Nickel
Shell Plating	Yellow Chromate over Zinc
Hardware	3,05 (.120) Through Holes
Contact Termination	Solder Cup
Shell Size	DC
Temperature Rating	-55°C to +125°C
Current Capacity	7.5 A
Contact Resistance	8 milli ohms max.

Sales Support

Ask a Specialist

Product Home

Stock Check

Dimensional Drawing

PRINTABLE PAGE

Dielectric Withstanding Voltage	1250 V AC at Sea Level
Reference Industry Specifications	Mil-PRF-24308
Insulator Material	Black Polyester UL 94V-0
Contact Material	Copper Alloy
Shell Material	Steel
Other Information	See Size 8 Contacts for Coax, High Power, and High Voltage Contacts

[Home](#)|[About ITT](#)|[Products](#)|[Design Center](#)|[Literature](#)|[News & Events](#)|[Search Tools](#)|[Global Sales Support](#)
© *ITT Corporation. All rights reserved.* [Legal Disclaimer](#)|[Privacy Policy](#)|[General Terms of Sale](#)
[Channel Partners Sign-In](#)