



[Home](#) | [Sign In](#) | [Contact Us](#)

SEARCH

Go



Standard D (Machined)

**PART NUMBER: DBMM25P**

Where Sold	Asia Pacific, Europe, Americas
Product Group	D-Subminiature
Product Sub-Family	D-Sub Standard
Component Type	Connector
Application Type	Military/High Reliability
Cable or PC Board	Cable
Gender	Plug
Number of Signal Pins	25
Number of Size 8 contacts	0
Straight or Right Angle	Straight
Contact Plating	50 micro inches Gold over Nickel
Shell Plating	Yellow Chromate over Zinc
Hardware	3,05 (.120) Through Holes
Contact Termination	Solder Cup
Shell Size	DB
Temperature Rating	-55°C to +125°C
Current Capacity	5 A
Contact Resistance	8 milli ohms max.
Dielectric Withstanding Voltage	1250 V AC at Sea Level
Reference Industry Specifications	Mil-PRF-24308
Insulator Material	Polyester
Contact Material	Copper Alloy
Shell Material	Steel



[Home](#) | [About ITT](#) | [Products](#) | [Design Center](#) | [Literature](#) | [News & Events](#) | [Search Tools](#) | [G Support](#)

© ITT Corporation. All rights reserved. [Legal Disclaimer](#) | [Privacy Policy](#) | [General Terms](#) | [Channel Partners Sign-In](#)