



Actual

Catalog Number: 15004-100
Product ID: 7TAD012820R0000
UPC Number: 03448123301
EAN Number: 05415022249002
Status: Active

3/8 Inch Gray Liquidtight Flexible Non-metallic Conduit, 100 Foot Coil

- Lightweight for easy handling, transportation and installation.
- Crush, abrasion and strain resistant.
- Provides superior wire protection
- Smooth interior ideal for pulling cable, no jagged edges.
- Maintains internal I.D. even in tight radius bends.
- Air conditioning and heating
- Computer power distribution
- Machine Tools
- Console wiring
- Transformer connections
- Outdoor lighting

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Carlton
Type	Liquidtight Flexible Non-Metallic Conduit & Fittings
Special Features	Non-Conductive and Non-Corrosive.
Application	Control and Motor
Standard	cULus E95745
Trade Size	3/8 Inch
Length	100 Feet
Material	PVC
Color	Gray

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal size in inch	3/8 inch
Material	PVC
Oil resistant	Y
Colour	Grey
Lengthwise slotted	N
Closable (two-part)	N
Approved according to UR	Y

Packaging

Outer Quantity	100
Outer Dimensions (inches)	19x19x4.5
Weight Uom	11.25 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com