



- [Home](#)
- [Latest Products](#)
- [Resources](#)
- [Product Documents](#)
- [Compliance Documents](#)
- [Download Catalog](#)

- [Trade Shows](#)
- [Warranty Policy](#)
- [Videos](#)
- [Where To Buy](#)

Search



Related Categories: [Wrenches](#) | [Wrenches](#)


RELATED PRODUCTS

CWRR-716 - Combo Wrench, Ratcheting, Reversible



This combination, ratcheting, reversible wrench measures 7/16" at both ends. A standard open end wrench (with a 15° offset) on one side and a ratcheting reversible box end (with a 15° angled head) on the other. The ratcheting end allows you to toggle from tightening to loosening. It provides 12 points of contact, making this the perfect wrench for cable and satellite installers working on "F" connectors, splitters, wall outlets and on the back of TV's. Made of chrome vanadium steel, chrome plated and polished to a high gloss finish.

Click to Zoom



SHARE PAGE

FIND A DISTRIBUTOR

- [Specifications](#)
- [Product Family](#)

Wrench Type	Combination, Ratcheting
Size	7/16"
Head Angle	15 Degrees
Finish	Polished
Weight	0.215 lbs
Length	6-1/2" (165.1mm)
UPC No.	811490016774



[ASW-R716 - Speed Ratcheting Wrench](#)



[ASWS-R716 - Ratcheting Speed Wrench](#)



JOIN OUR MAILING LIST

JOIN!

Email Address

- [ABOUT US](#)
- [BLOG](#)
- [CONTACT US](#)

Jonard Tools 134 Marbledale Road Tuckahoe, NY 10707 Tel: 914.793.0700 Fax: 914.793.4527
Email: sales@jonard.com