

Datasheet

RS Pro 3.6V, 4000mAh NiCd D Rechargeable Battery Pack

RS Stock No: **195-1303**



Product Details

RS Pro NiCd rechargeable battery of D size, has 4000 mAh of battery capacity to power up a device. This battery has a nominal voltage of 3.6 V and is perfect to use as replacement battery for safety lighting units. It has high charge efficiency at high temperature. The battery is perfect to work within the temperature range of -20 to +65°C.

Features and Benefits

- D size
- NiCd rechargeable battery
- 4000 mAh battery capacity
- 3.6 V of nominal voltage
- Used as replacement batteries for safety lighting units

**Specifications:**

Chemistry	NiCd
Size	D
Capacity	4000 mAh
Dimensions	32.3 x 60.3 mm
Maximum Continuous Current	20 A
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-20°C
Nominal Voltage	3.6 V
Number of Cells	3
Operating Temperature Range	-20 to +70°C
Size	D
Weight	132 g