



ENGLISH

Datasheet

Stock No: 199-781

RS Pro 1.2V NiMH Tagged Terminal D Rechargeable Battery, 7000mAh



Product Details

RS Pro, High Temperature Tagged

For use in emergency lighting units and back-up applications Voltage 1.2V

Note

All batteries are supplied with only a residual charge and should be charged at the continuous charge rate before use

Caution

Do not connect batteries in parallel

NiMH Rechargeable Industrial Batteries

Improved performance over NiCd batteries.



Specifications

Chemistry	NiMH
Capacity	7000mAh
Size	D
Terminal Type	Tagged
Nominal Voltage	1.2V
Dimensions	58.5 x 32.2mm
Operating Temperature Range	0 → +70°C
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	0°C