


BCC M324-M314-30-304-EX44T2-003
BCC0H3W



4MT5
(CJ/VV CABLE ASSEMBLY)

Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	TPE yellow, 0.30 m, Drag chain compatible
Cable diameter D	5.30 mm ±0.13 mm
Cable, bending cycles min.	10 million
Conductor cross-section	AWG 22
Number of conductors	4
Number of pins	4/4
System	Molded/Molded

Electrical data

Cable rated voltage AC max.	300.0 V
Cable rated voltage DC max.	300.0 V
Rated current (40 °C)	4.0 A

Environmental conditions

Cable temperature, fixed routing	-50...105 °C
Cable temperature, flexible routing	-25...105 °C

Protection type IEC 60529

IP67 /IP67

General data

Approval/Conformity cULus LISTED

Material

Material contact carrier	PUR/PUR
Material contacts	Bronze/Brass
Material cover nut	Die-cast zinc/Die-cast zinc
Material grip	TPU/TPU

Mechanical data


Tightening torque pigtail 0.4 Nm/0.4 Nm

Remarks


Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.
Cable construction acc. to UL-AWM Style 2037

BCC M324-M314-30-304-EX44T2-003
BCC0H3W

Connector view



I PIN 1: brown PIN 2: white PIN 3: blue PIN 4:
black



II PIN 1: brown PIN 2: white PIN 3: blue PIN 4:
black

Wiring Diagram

