

BES R04KC-PSC25F-EP02 BES01YN

Range/Distance

Assured operating distance Sa	2.2 mm
Range	2.5 mm
Rated operating distance Sn	2.5 mm
Ripple max. (% of Ue)	15 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %

Remarks

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.

Wiring Diagram

