

ENGLISH

Datasheet

RS Pro NiMH AAA Rechargeable Battery, 800mAh

RS Stock No: 504-6051



Product Details

RS Pro NiMH rechargeable battery of D size, has 800 mAh of battery capacity to power up a device. This battery has a nominal voltage of 1.2 V and is suitable for general purpose applications. The battery is perfect to work within the temperature range of -10 to +60°C.

Features and Benefits

- AAA size
- NiMH rechargeable battery
- 800 mAh battery capacity
- 1.2 V of nominal voltage
- Suitable for general purpose applications



ENGLISH

Specifications:

Chemistry	NiMH
Size	AAA
Terminal Type	Standard
Capacity	800 mAh
Dimensions	10.3 x 44.3 mm
Maximum Continuous Current	3 mA
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-10°C
Nominal Voltage	1.2 V
Operating Temperature Range	-10 to +60°C
Size	AAA