

CABLE-D25SUB/B/2X14/100/TU812

Order No.: 2304649



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2304649>

Splitting cable for ABB S800 I/O, cable length 1 m

Commercial data

EAN	4017918951368
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.1637 KG
Catalog page information	Page 189 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 Ω /m
Ambient temperature (operation)	-20 °C ... 50 °C

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions, control side	25
Number of connectors, control side	1
Number of positions, module side	14
Number of connectors, modul side	2
Fixed cable length	1 m
Single wire, cross section	0.14 mm ²
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	6.3 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

Address

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>



© 2009 Phoenix Contact
Technical modifications reserved;