



Actual

Catalog Number: 54105UF
Product ID: 7TAH007110R0000
UPC Number: 78621088690
Status: Active

Copper One-Hole Lug, 45 Degree Bend Standard Barrel, Max 35kV, #6 AWG Wire, 1/4 Inch Bolt Size, Tin Plated, Die Code 24, Die Color Code Blue

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel Copper Lug
Standard	UL E9809
Cable Size	#6 AWG
Stud Size	1/4 Inch
Number Of Holes	1
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	45°
Slender flange model	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	50
Inner Dimensions (inches)	3.5x2.8x2.5
Outer Quantity	500
Outer Dimensions (inches)	12.2x6.4x4.1
Weight Uom	1.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00675-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com