

## 4 Socket Individually Switched Extension Lead



### FEATURES

- Manufactured to BS1363-2
- Rewirable
- Safety socket shutters
- Wall fixing option
- Individual switched for power control of connected products
- Power indicator for visible power status

### TECHNICAL SPECIFICATIONS

Standard(s)	This product is certified to applicable British safety standards BS1363/A(Socket & Plug), BS1362(Fuse), BS6500(Flex)	CE
Socket Dimension	Length 315mm x Width 49mm x Height 20mm	
Distance Between Sockets	60mm	
Wall Mounting Option	Yes	
Maximum Load (Wattage)	10A : 2400 Watts, 240 Volts. 13A : 3120 Watts, 240 Volts	
Flexible Cable	3 Core 1.25mm <sup>2</sup> Stranded	
Sockets	4 UK 13 Amp sockets Individually switched Safety shutters Re-wireable	
Terminal Capacity	1 x 1.5mm <sup>2</sup> Stranded	
Material	Thermoplastic socket & plug bodies Brass contacts	

IF IN DOUBT CONSULT A QUALIFIED ELECTRICIAN

### USER INSTRUCTIONS

PLEASE READ CAREFULLY AND USE IN ACCORDANCE WITH OUR SAFETY INSTRUCTIONS BELOW

- ✓ **DO** Uncoil cable before use
- ✓ **DO** Position the cable carefully to avoid accidents
- ✗ **DON'T** Use in wet conditions
- ✗ **DON'T** Allow heavy tools etc to hang unsupported on the cable or from the socket
- ✗ **DON'T** Remove the plug and wire directly into a mains supply
- ✗ **DON'T** Exceed the total maximum load.