







# Datasheet

## Thread-Forming Screw

RS Stock number: 482-7764

Dimensions(mm):



		HEAD DIMENSIONS															
METRIC	GAUGE	DIN 7504 - N		DIN 7504 - P		DIN7504 - K				DIN7504 - Q		DIN7504 - L				DIN 7504 Similar	
																	
		Pan		Csk (80°)		Indented Washer Hex				Raised Csk (80°)		Indented Washer Hex				Flange	
		MAX	MIN	MAX	MIN	HEX A/F Max.	HEX Depth Min.	Washer Dia. Max.	Total Depth Max.	MAX	MIN	HEX A/F Max.	HEX Depth Min.	Washer Dia. Max.	Total Depth Max.	DIA* MAX	DEPTH MAX
2.9	4	5.6	5.35	5.5	5.25	-	-	-	-	5.5	5.20	-	-	-	-		
3.5	6	6.9	6.6	6.8	6.5	5.5*	1.55	8.3	3.45	6.8	6.44	5.5	1.55	8.3	3.45		
3.9	7	7.5	7.2	7.5	7.2	5.5*	1.55	8.3	3.45	7.5	7.14	5.5	1.55	8.3	3.45		
4.2	8	8.2	7.9	8.1	7.8	7.0*	1.9	8.8	4.25	8.1	7.74	7.0	1.9	8.8	4.25	10.92	2.36
4.8	10	9.5	9.2	9.5	9.2	8.0	2.0	10.5	4.45	9.5	9.14	8.0	2.0	10.5	4.45		
5.5	12	10.8	10.5	10.8	10.5	8.0	2.7	11.0	5.45	10.8	10.37	8.0	2.7	11.0	5.45		
6.3	14	12.5	12.14	12.4	12.04	10.0	3.3	13.2	6.45	12.4	11.97	10.0	3.3	13.2	6.45		