

Datasheet

## RS Pro 1/2 in G 12mm 490mm Hose Reel 16 bar, Wall Mounting

RS Stock No: **495-2078**



### Product Details

RS Pro hose reel features heavy duty UV stabilised polypropylene outer casings. This lightweight, corrosion proof hose reel is designed for wall mounting. It has maximum working pressure of 16 bar and 1/2 Inch G inlet connection.

### Features and Benefits

- Spring driven retractable hose reel
- Lightweight, corrosion proof and virtually maintenance free
- Designed for wall mounting and comes with pivoting wall bracket



ENGLISH

### Specifications:

Hose Included	Yes
Inlet Connection	1/2 in G
Inlet Thread Standard	BSPT
Mounting	Wall Mount
Retraction Operation	Automatic
Hose Inner Diameter	12 mm
Hose Length	18 m
Inlet Connection Size	1/2 in
Reel Diameter	490 mm
Maximum Working Pressure	16 bar
Material	PP