

Datasheet


ENGLISH


RS, Brown Wall Cabinet Speaker, 8Ω

RS Stock number: 425-4504



- 1. Unpack Loudspeaker.
- Remove hanging bar from restraining wire.
- 3. Use the hanging bar as a jig to mark hole locations on wall.
- Secure hanging bar to wall using suitable fixings (fit hanging bar to wall the correct way round as shown).






- Re attach the restraining wire to hanging bar.
- 2. Adjust the transformer wattage by moving the grey wire to the desired taping on the terminal-block.(this is tapped to the 4w as standard)
- 3. Connect 100V line input to terminal block + -.
- Fit cabinet over hanging bar.


RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH



Kestrel 4 with Restoration Connections



Technical specifications

Cabinet Size:

H 200mm W 250mm D 85mm

Power Taps:

4W 2W 1W .5W .25W .125W

Frequency Range:

150Hz - 15kHz

SPL:

86dB(A) at 1watt/ 1 meter

Line Voltage:

100V

Loudspeaker Impedance:

 Ω 8