



Datasheet

ENGLISH

Stock No: 541-5255

RS Pro DC Axial Fan, 80 x 80 x 15mm, 32.3m³/h, 2.4W, 24 V dc (OD8015 Series)



Product Details

RS Brushless High Performance Ball Bearing Fan

RS brushless high performing ball bearing fans provide a general purpose, compact, cost-effective and reliable solution to a variety of requirements.

Black construction

Approvals

UL, cUL, TUV



ENGLISH

Specifications:

Supply Voltage	24 V dc
Dimensions	80 x 80 x 15mm
Height	80mm
Width	80mm
Depth	15mm
AC or DC Operation	DC
Air Flow	32.3m ³ /h
Power Consumption	2.4W
Maximum Current	100mA
Bearing Type	Ball
Noise Level	20dB
Fan Speed	2000rpm
Series	OD8015