

ENGLISH

Datasheet

RS Pro Steel Drop-In Anchor M6, fixing hole diameter 8mm, length 25mm

RS Stock No: **622-2127**



Product Details

RS Pro stainless steel drop-in anchor with M6 threading size, is compatible with concrete with a compressive strength greater than 20 N/mm2. This anchor measures 25 mm long and is suitable for 8 mm fixing hole diameter.

Features and Benefits

- A deformation controlled anchor system
- Suitable for use in concrete
- Compressive strength greater than 20N/mm2
- 8 mm fixing hole diameter
- 25 mm long



ENGLISH

Specifications:

Material	Steel
Type	Drop In Anchor
Fixing Hole Diameter	8 mm
Length	25 mm
Thread Size	M6
Finish	Zinc Plated, Yellow Passivated
Internal Thread Length	10 mm
Minimum Hole Depth	25 mm