



ENGLISH

Datasheet

RS Pro Cartridge Fuse, F, 0.1A, 5 x 20mm

RS Stock No: **610-9579**



Product Details

RS Pro cartridge fuse is current rated for 0.1 A. This glass bodied, F-speed fuse has nickel plated brass ends.

**Specifications:**

Body Material	Glass
Breaking Capacity (at Maximum Voltage Rating)	35 A
Current Rating	0.1 A
Diameter	5.2 mm
Fuse Speed	F
High Rupture Capacity	No
Includes Indicator	No
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-25°C
Operating Temperature Range	-25 to +70°C
Overall Dimensions	5.2 x 20 mm
Overall Length	20 mm
Size Designation	Miniature
Voltage Rating	250 V
Standards Met	UL, VDE, SEMKO, BEAB, DIN 4166, IEC 127-2/II and EN 60127-2/II, RoHS Compliant