

Datasheet

Grey 20 A Grey Wall Switch Rocker Surface, 2 Way Screwed Matte, 1 Gang BS Standard, 250 V 91mm LED IP66 Polycarbonate 1
RS Stock number: 699-7076



Features

Clearly marked terminals with backed out captive screws for easy installation

20 Amp, 20AX inductive rated

Covers to seal the fixing screws

Earth terminal in mounting box

All cable entries in the 4 sides have removable blanking caps.

Housing will accept alternative switch modules from the Grid range

Neon indicator that can be wired to illuminate when off or on depending on wiring

Technical Specifications (WP12, WP14, WP42 products)

Standard(s)	BS EN 60669-1
Rating	20 Amp 250V~ (20AX - no derating for inductive or fluorescent loads)
Switch type	Single pole
Contact Gap	3.0mm minimum
Terminal Capacity	4 x 1.0mm ² 4 x 1.5mm ² 2 x 2.5mm ² 1 x 4.0mm ²
IP rating	IP66
Covered by RoHS directive	No
Covered by WEEE directive	No
Size	91mm x 91mm x 67mm
Number of 20mm cable entries	5 x 20mm. 1 in each of 3 sides and 2 in the remaining side 1 drill out entry 20/25mm in rear face

Technical Specifications (WP30 products)

Standard(s)	BS EN 60669-1
Rating	20 Amp 250V~ (20AX - no derating for inductive or fluorescent loads)
Switch type	Double pole
Contact Gap	3.0mm minimum
Terminal Capacity	4 x 1.0mm ² 4 x 1.5mm ² 2 x 2.5mm ² 1 x 4.0mm ²
IP rating	IP66
Covered by RoHS directive	No
Covered by WEEE directive	IP66
Size	91mm x 91mm x 67mm
Number of 20mm cable entries	5 x 20mm. 1 in each of 3 sides and 2 in the remaining side 1 drill out entry 20/25mm in rear face

