

Datasheet

RS Pro 2kW Oil Filled Radiator, Floor Mounted, Type G - British 3-pin

RS Stock No: **712-6070**



Product Details

RS Pro 2 kW oil filled radiator has type G - British 3-pin plug for connection and is floor mountable. This oil filled radiator features efficient floor standing wheels for easy rolling movement.

Features and Benefits

- Efficient floor standing wheels
- Variable thermostatic control
- Floor mountable

**Specifications:**

Control Type	Thermostat
Depth	165 mm
Dimensions	660 x 370 x 165 mm
Heat Type	Convection
Height	660 mm
Maximum Output Power	2 kW
Mounting	Floor Mounted
Plug Type	Type G - British 3-Pin
Power Settings	3
Width	370 mm