

Datasheet

RS Pro Inline RCD Non-Latching 2 Pole, Tripping Time 40ms, Tripping Current 30mA, Rated At 13A, 240 V ac

RS Stock No: 750-8450



Product Details

RS Pro non-latching inline RCD adapter provides added protection against electrocution. The double pole switching isolates both live and neutral when contacts trip. This inline RCD plug will continuously monitor the power supply to an electrical appliance and will cut the power within 40 milliseconds if an earth current fault is detected. The adapter has a current rating of 13 A and voltage rating of 240 V ac. It has IP65 rating protection for added safety.

Features and Benefits

- Provides added protection against electrocution
- Double pole switching
- Continuously monitor the power supply to an electrical appliance
- 40 milliseconds of tripping time
- 30 mA tripping current
- 13 A current rating
- 240 V ac voltage rating

**Specifications:**

Current Rating	13 A
Inline	Yes
IP Rating	IP65
Pole Format	2
Tripping Current	30 mA
Tripping Time	40 ms
Type	Non-Latching
Voltage Rating	240 V ac
Maximum Load	3120 W
Standards Met	BS7071:1992