



Datasheet

ECP15 series


Constant Voltage Led Power Supply

ENGLISH



Features

- Input Voltage: 200 – 240Vac
- Output Power: 15W
- Compact and light-weight plastic case
- Working Temperature: -20C to +45C
- Protections: short circuit/overload/overheat
- 1 year warranty



Part number	Voltage	Load	Max Output Current	PF	L x W x H
764-7151	12	0-15W	1.25A	>0.5	123 x 45 x 20 mm
764-7154	24	0-15W	0.625A		

Mechanical specification

Designed to meet Safety:

- EN61347-1
- EN61347-2-13
- EMI to EN55015
- EMS to:
- EN61000-3-2
- EN61000-3-3
- EN61547

