



Datasheet

ECP50 series


Constant Voltage Led Power Supply

ENGLISH



Features

- Input Voltage: 200 – 240Vac
- Output Power: 50W
- Compact and light-weight plastic case
- Working Temperature: -20C to +45C
- Protections: short circuit/overload/overheat
- Power factor corrected
- 1 year warranty



Part number	Voltage	Load	Max Output Current	PF	L x W x H
764-7160	12	0-50W	4.17A	0.9	185 x 64 x 22 mm
764-7164	24	0-50W	2.08A		

Mechanical specification

Designed to meet Safety:

- EN61347-1
- EN61347-2-13
- EMI to EN55015
- EMS to:
 - EN61000-3-2
 - EN61000-3-3
 - EN61547

