



ENGLISH

Data Sheet Cable Reel

10 Meter Cord 3G 1.0mm² German Type

RS Stock No. 768-4444



Electrical Specification:

Rated voltage: 230VAC

Rated current (Full-reeled): 4.8A

Rated power (Full-reeled): 1100W

Rated current (Unreeled): 10A

Rated power (Unreeled): 2300W

Special Feature:

Cable reel semi-enclosed

German Type

4 way DIN49440-1 socket outlet

1 non-rewirable plug, 16A, 250V~

DIN49441-R2

10m cord, H05VV-F 3G1.0mm²

1 Thermal cut-out, 16(6A), 250Vac

1000 cycle, single pole

Category D With shutter

Outer Dia: ϕ 230mm