

## Datasheet

# RS Pro White 2 Gang Urea Formaldehyde Unswitched Electrical Socket, Type G - British, 13A, Flush Mount, IP20

RS Stock No: **775-8071**



## Product Details

RS Pro 2-gang unswitched power socket has urea formaldehyde construction. This type G - British socket in white colour, has matte finishing. It is suitable industrial, commercial and workshop applications with a current requirement of up to 13 A. The IP20 rated device offers superior protection.

## Features and Benefits

- 13 A socket
- Flush mount
- Comes in matte white finish

**Specifications:**

Colour Family	White
Colour	White
Current Rating	13 A
Earth Terminal	Yes
Faceplate Depth	7 mm
Faceplate Mounting Type	Screwed
Finish	Matt
Fixing Standard	BS
International Protection Rating	IP20
Material	Urea Formaldehyde
Minimum Box Depth	25 mm
Mounting Style	Flush Mount
Number of Gangs	2
Number of Modules	2
Number of Poles	0
Overall Dimensions	146 x 86 mm
Overall Height	146 mm
Overall Width	86 mm
Socket Type	Type G - British
Switched	No
Terminal Type	Screw
Voltage Rating	230 V ac