

Datasheet

RS Pro 13A 2 Gang Switched Wall Mount Fused Spurs

RS Stock No: **775-8084**



Product Details

RS Pro 2-gang switched wall mount fused spurs in white colour, have a current rating of 13 A. This BS 1363 spurs have urea formaldehyde construction, which is water resistant, strong and permanent.

Features and Benefits

- Current rating of 13 A
- Urea formaldehyde construction
- Wall mountable

Specifications:

Colour	White
Current Rating	13 A
Depth	33 mm
Dimensions (L x W x D)	85.6 x 85.6 x 33 mm
Faceplate Depth	7 mm
Finish	Matte
Fixing Standard	BS Standard
Fuse Type	BS 1363
Height	85.6 mm, 86 mm
Length	85.6 mm
Material	Urea Formaldehyde
Minimum Box Depth	25 mm
Mounting Style	Wall Mount
Number of Gangs	2
Number of Poles	2
RCD Type	None
Switched	Yes
Width	85.6 mm