

**Professionally approved products.**

## Datasheet

### VGA Splitter (2 Port)

RS Stock number 783-9852



<b>Short Description</b>	VGA Splitter, 450Mhz, up to 65Mtr
<b>Full Description</b>	<p>The NLKVS-range of Video Splitters are designed for desktop use, supplied in a durable, compact metal housing. The splitters duplicate and boost the input signal to 2, 4 or 8 VGA, SVGA or Multi-sync Monitors, with a signal rate of <b>450 Mhz</b>. Video Splitters are ideal for applications such as tradeshows, business meetings and demonstrations.</p> <p>These products are independent of software and other than cables and Monitors, no additional hardware is required.</p>
<b>Extra Information</b>	<p><b>Specification</b></p> <ul style="list-style-type: none"> <li>250 - 450Mhz Video Bandwidth</li> <li>Supports up to 2048 x 1536 Resolution</li> <li>Supports DDC, DDC2 &amp; DDC2B(Port 1 only)</li> <li>Duplicate one signal input to multiple outputs</li> <li>Ability to be cascaded</li> <li>Effective transmission distance: 65 Mtrs</li> <li>Power saving mode</li> <li>Metal Case</li> </ul> <p><b>Contents</b></p> <ul style="list-style-type: none"> <li>1 x Video Splitter</li> <li>1 x Power Supply</li> <li>1 x User Manual</li> </ul>