

Datasheet

RS Pro Stainless Steel Drop-In Anchor M10, fixing hole diameter 12mm, length 40mm

RS Stock No: **622-1720**



Product Details

RS Pro stainless steel drop-in anchor with M10 threading size, is compatible with concrete with a compressive strength greater than 20 N/mm². This anchor measures 40 mm long and is suitable for 12 mm fixing hole diameter.

Features and Benefits

- A deformation controlled anchor system
- Suitable for use in concrete
- Compressive strength greater than 20N/mm²
- Fixing hole diameter of 12 mm
- 40 mm length



Specifications:

Material	Stainless Steel
Type	Drop In Anchor
Fixing Hole Diameter	12 mm
Length	40 mm
Thread Size	M10
Grade	316 (A4)
Internal Thread Length	15 mm
Minimum Hole Depth	40 mm