

ENGLISH

Datasheet

RS Pro Stainless Steel Drop-In Anchor M16, fixing hole diameter 16mm, length 65mm

RS Stock No: 622-1758



Product Details

RS Pro stainless steel drop-in anchor with M16 threading size, is compatible with concrete with a compressive strength greater than 20 N/mm2. This anchor measures 65 mm long and is suitable for 16 mm fixing hole diameter.

Features and Benefits

- A deformation controlled anchor system
- Suitable for use in concrete
- Compressive strength greater than 20N/mm2
- Fixing hole diameter of 16 mm
- 65 mm long



ENGLISH

Specifications:

Material	Stainless Steel
Type	Drop In Anchor
Fixing Hole Diameter	16 mm
Length	65 mm
Thread Size	M16
Grade	316 (A4)
Internal Thread Length	25 mm
Minimum Hole Depth	60 mm