



ENGLISH

Datasheet

## RS Pro Stainless Steel Bolt Anchor M8, fixing hole diameter 8mm, length 95mm

RS Stock No: 622-1950



### Product Details

RS Pro captive stud through bolt anchor made of A4-316 grade stainless steel resist corrosion. This bolt anchor is suitable for use in concrete with a compressive strength greater than 20 N/mm<sup>2</sup>. The bolt anchor measures 95 mm long with M8 threading that is suitable for 8 mm fixing hole diameter.

### Features and Benefits

- Captive stud through bolt anchor
- A4-316 grade stainless steel construction
- Suitable for use in concrete over 20N/mm<sup>2</sup>
- 8 mm fixing hole diameter
- 95 mm long



**Specifications:**

Material	Stainless Steel
Type	Captive Stud Through Bolt Anchor
Fixing Hole Diameter	8 mm
Length	95 mm
Maximum Fixing Thickness	30 mm
Thread Size	M8
Grade	316 (A4)
Minimum Hole Depth	65 mm