

Datasheet

RS Pro Stainless Steel Bolt Anchor M10, fixing hole diameter 10mm, length 85mm

RS Stock No: **622-1966**



Product Details

RS Pro captive stud bolt anchor made of A4-316 grade stainless steel resist corrosion. This bolt anchor is suitable for use in concrete with a compressive strength greater than 20 N/mm². The bolt anchor measures 85 mm long with M10 threading that is suitable for 10 mm fixing hole diameter.

Features and Benefits

- Captive stud through bolt anchor
- A4-316 grade stainless steel construction
- Suitable for use in concrete over 20N/mm²
- 10 mm fixing hole diameter
- 85 mm long



Specifications:

Material	Stainless Steel
Type	Captive Stud Through Bolt Anchor
Fixing Hole Diameter	10 mm
Length	85 mm
Maximum Fixing Thickness	10 mm
Thread Size	M10
Grade	316 (A4)
Minimum Hole Depth	65 mm