

Datasheet

RS Pro Stainless Steel Masonry Fixing M12, fixing hole diameter 12mm, length 145mm

RS Stock No: **622-2004**



Product Details

RS Pro masonry fixing captive stud bolt anchor is made of A4-316 grade stainless steel for corrosion resistance. This bolt anchor is suitable for use in concrete with a compressive strength greater than 20 N/mm². The anchor measures 145 mm long with M12 threading that is suitable for 12 mm fixing hole diameter.

Features and Benefits

- Captive Stud Through Bolt Anchor
- A4-316 grade stainless steel construction
- Suitable for use in concrete over 20N/mm²
- Fixing hole diameter of 12 mm
- 145 mm long



Specifications:

Material	Stainless Steel
Type	Captive Stud Through Bolt Anchor
Fixing Hole Diameter	12 mm
Length	145 mm
Maximum Fixing Thickness	50 mm
Thread Size	M12
Grade	316 (A4)
Minimum Hole Depth	90 mm