

ENGLISH

Datasheet

RS Pro Horizontal Mounting Float Level Switch, -40°C to +125°C RS Stock No: 762-1039

Product Details

RS Pro horizontal mounting float level switch has an operating temperature range of -40 to +125°C. This switch is suitable for use with water, acids and oils and acceptable for use in contact with food.

Features and Benefits

- Stainless steel body
- Operating temperature of -40 to +125°C
- Suitable for use with water, acids and oils and acceptable for use in contact with food



ENGLISH

Specifications:

Body Material	Stainless Steel
Cable Length	300 mm
Device Type	Float
Gasket Material	Silicone
Maximum AC Voltage	250 V ac
Maximum Current	0.5 A
Maximum DC Voltage	200 V dc
Maximum Operating Temperature	+125°C
Maximum Pressure	10 bar
Minimum Operating Temperature	-40°C
Mounting Type	Horizontal
Switch Output	NO/NC
Maximum Carry Current	2 A
Maximum Switching Current	1.5 A