



ENGLISH

Datasheet

25m Long Red Rubber Hose, Applications Acetylene Gas, 10mm Inner Diam.

RS Stock number 486-463

Type : Welding Hose

Type No. : 2801

Application : Acetylene

Standard Length : 50

Description :

Lightweight, flexible, smooth, red hose for acetylene, to EN559. For use with industrial autogenic welding equipment, usually together with blue oxygen hose. Also ideal for natural gas and air. Please contact Codan for further information.

Working Temperature : -25°C to +80°C

Std. Branding : CODAN 2801 - EN 559 - 2 Mpa (20 bar)
- dim - year - sn.

Reinforcement : Ester

Inside : SBR

Colour : Black

Outside : EPDM

Colour : Red

Standards : EN 559: 2003

Data

Inside dia. mm	Outside dia. mm	Working Pressure BAR	Burst Pressure BAR	Bend Radius mm	Weight g/m	Product number
6.3	13.3	20	60	63	146	2801006
8.0	14.6	20	60	80	172	2801008
10.0	17.0	20	60	100	203	2801010
12.5	19.4	20	60	125	257	2801013
20.0	27.2	20	60	200	399	2801019

Illustration

